



Weighting arms for roving frames



Precision components for spinning machines

Quality • Reliability • Innovation

Weighting arms for roving frames

TeraSpin weighting arms are characterised by their robust design and corrosion resistant finish. These weighting arms are built to last the lifetime of the ring frame or roving frame. The loading springs used on TeraSpin weighting arms are pre-calibrated for specified loads and last a life time. Each weighting arm exerts the same load on top rollers irrespective of how long they are in use or at what position in the machine they are fastened.


Features

- Reliable loading through leveraged force of helical coil springs
- Available in 3-roller and 4-roller drafting configurations
- Choice of load selection on each top roller
- New ergonomics design of knob

Benefits

- Consistent quality of yarn
- No height gauge setting required after cot buffing within the specified range of cot diametres
- Free from vagaries of pneumatic pressure loss or pressure variations
- Suitable for a wide variety of fibres and yarn counts
- · Virtually maintenance-free
- Long service life

Weighting arm PK 1500-0962604 YB & PK 1500-0962604 SB



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/25*/28	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	27 - 30	28/25*/28	37 X 40 X 0.9 ⁿ
OH P 310	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ^{tt}
OH 534-1275268	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ^x
OH 534-000110	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ⁿ
OH 524-000110	55 - 60	30 - 32	35/33*/35	57.2 X 40 X 0.9

Roller	Weighting	Top r	oller load ii	n daN
position	element	Black	Green	Red
Front	ME 5	20	25	30
Middle (with apron)	XM 5-1	10	15	20
Rear	RG 5	15	20	25

Top roller at front and back position	Apron top roller	
LP 315-000110	LP 317-000110	

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 3-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 15000962604 SR



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/25*/28	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	27 - 30	28/25*/28	37 X 40 X 0.9 ⁿ
OH P 310	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ^{tt}
OH 534-1275268	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ^x
OH 534-000110	45 - 54	30 - 32	35/33*/35	48 X 40 X 0.9 ⁿ
OH 524-000110	55 - 60	30 - 32	35/33*/35	57.2 X 40 X 0.9

Roller	Weighting	Top r	oller load i	n daN
position	element	Black	Green	Red
Front	ME 5	20	25	30
Middle (with apron)	XM 5-1	10	15	20
Rear	RG 5	15	20	25

Top roller at front and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 3-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0962602 YB & PK 1500-0962602 SB



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	30	35/25*/35	37 X 40 X 0.9 ^m
OH 514-1275261	Up to 44 max.	30	35/25*/35	37 X 40 X 0.9 ⁿ
OH P 310	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9 ^a
OH 534-1275268	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9 ^a
OH 534-000110	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9 ^a
OH 524-000110	55 - 60	30 - 32	35/25*/35	52.7 X 40 X 0.9

Roller	Weighting element	Top r	oller load in	n daN
position		Black	Green	Red
Front	ME 5	20	25	30
Middle (with apron)	XM 5-1	10	15	20
Rear	RG 5	15	20	25

Top roller at front and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- ¤ One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 3-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0962602 SR



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	30	35/25*/35	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	30	35/25*/35	37 X 40 X 0.9 ^{tt}
OH P 310	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9 ^a
OH 534-1275268	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9 th
OH 534-000110	45 - 54	30 - 32	35/25*/35	43.5 X 40 X 0.9°
OH 524-000110	55 - 60	30 - 32	35/25*/35	52.7 X 40 X 0.9 ⁿ

Roller	Weighting	Top r	oller load ii	n daN
position	element	Black	Green	Red
Front	ME 5	20	25	30
Middle (with apron)	XM 5-1	10	15	20
Rear	RG 5	15	20	25

Top roller at front and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- ¤ One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 3-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0001938 YB & PK 1500-0001938 SB



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/28/25*/28	37 X 40 X 0.9 [¤]
OH 514-1275261	Up to 44 max.	27 - 30	28/28/25*/28	37 X 40 X 0.9 ⁿ

Roller	Weighting	Тор	ı daN	
position	element	Black	Green	Red
Front	XR 5	9	12	15
2 nd	RG 5	15	20	25
3 rd (with apron)	XM 5-1	10	15	20
Rear	XM 5	10	15	20

Top roller at front, 2 nd and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- ** Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- ¤ One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 4-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0001938 SR



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/28/25*/28	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	27 - 30	28/28/25*/28	37 X 40 X 0.9 [¤]

Roller	Weighting	Тор	roller load in daN		
position	element	Black	Green	Red	
Front	XR 5	9	12	15	
2 nd	RG 5	15	20	25	
3 rd (with apron)	XM 5-1	10	15	20	
Rear	XM 5	10	15	20	

Top roller at front, 2 nd and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- m One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 4-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0001940 YB & PK 1500-0001940 SB



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/25*/28/28	37 X 40 X 0.9 ^m
OH 514-1275261	Up to 44 max.	27 - 30	28/25*/28/28	37 X 40 X 0.9 [¤]

Roller	Weighting	Тор	Top roller load in daN		
position	element	Black	Green	Red	
Front	ME 5	20	25	30	
2 nd (with apron)	XM 5-1	10	15	20	
3 rd	RG 5	15	20	25	
Rear	RG 5	15	20	25	

Top roller at front, 3 rd and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- m One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 4-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1500-0001940 SR



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 30	28/25*/28/28	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	27 - 30	28/25*/28/28	37 X 40 X 0.9 [¤]

Roller	Weighting	Тор	roller load in daN		
position	element	Black	Green	Red	
Front	ME 5	20	25	30	
2 nd (with apron)	XM 5-1	10	15	20	
3 rd	RG 5	15	20	25	
Rear	RG 5	15	20	25	

Top roller at front, 3 rd and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- * * Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- ¤ One can use aprons of different thicknesses


Application/s

Machine/s : Roving frame with 4-roller-double apron

drafting system

Process/s : Spinning

Weighting arm PK 1600-40 YB & PK 1600-40 SB



Combination of cradle and top rollers

Cradles	Fibre length (mm)	Bottom roller ø (mm) #	Top cot ø (mm) **	Recommended top apron size (mm)@
OH P 110	Up to 44 max.	27 - 32	28/25*/28/28	37 X 40 X 0.9 ⁿ
OH 514-1275261	Up to 44 max.	27 - 32	28/25*/28/28	37 X 40 X 0.9 ⁿ
OH P 310	45 - 54	27 - 32	35/33*/35/35	48 X 40 X 0.9 ⁿ
OH 534-1275268	45 - 54	27 - 32	35/33*/35/35	48 X 40 X 0.9 ^{tt}
OH 534-000110	45 - 54	27 - 32	35/33*/35/35	48 X 40 X 0.9 ^{tt}
OH 524-000110	55 - 60	27 - 32	35/33*/35/35	57.2 X 40 X 0.9 g

Roller	oller Weighting Top roller load in da			daN
position	element	Black	Green	Red
Front	ME 5	20	25	30
2 nd (with apron)	XM 5-1	10	15	20
3 rd	XM 5	10	15	20
Rear	XM 5	10	15	20

Top roller at front, 3 rd and back position	Apron top roller
LP 315-000110	LP 317-000110

- # Dia. of bottom rollers depends on machine manufacturers
- ** Top roller cot dia. indicates the dia. of newly mounted cots and they are not in the scope of supply
- @ Aprons are not in the scope of supply
- * It is recommended to keep the cot diameter on the lower side (up to 0.3 mm less) to allow free rotation of aprons
- m One can use aprons of different thicknesses

Application/s

Machine/s : Roving frame with 4-roller-double apron

drafting system

Process/s : Spinning





A.T.E. ENTERPRISES PRIVATE LIMITED

(Business Unit: TeraSpin)

Survey no. 251, Sarkhej Bavla Highway (N.H. no. 8A), Village: Sari

Taluka: Sanand, Ahmedabad 382 220, Gujarat, India

T: +91-2717-699061 E: sales@teraspin.com W: www.ategroup.com/teraspin

